WHIPPED CREAM DISPENSER

- Includes 3 decorating tips to create unique dessert and beverage presentations, and a brush to clean them
- Capacity: 1 Pint (0.5L)
- Fits standard 8gm N2O cartridge (not included); compatible with all brands of whipped cream cartridges
- Durable aluminum bottle with stainless steel handle
- Hand-wash only

ITEM	DESCRIPTION	SIZE	UOM	CASE
CW-A05	Whipped Cream Dispenser with 3 Decorating Tips	3" Dia x 12"H	Each	1/12
CW-P	3 Tips With 1 Cleaning Brush		Set	1
CW-PG	Replacement Gasket, 3-Pcs/Pk		Pack	1





MANDOLINE SLICERS

MDL-BLD

MDL-HD

SLICE BLADE

JULIENNE BLADE

.................

JULIENNE BLADE

Built-in blade styles and thicknesses

ATE BLADE

D PREPARATION

PREMIUM MANDOLINE SLICERS

- MDL-18 features rubberized handle for a non-slip grip and rotary side dial for precise thickness control.
- Includes three (3) built-in blade styles at varying thicknesses:
- SLICE 1/8", 1/4", 3/8"
- SERRATED/WAFFLE 1/8", 1/4", 3/8"
- ◆ JULIENNE 1/8", 3/8"
- MDL-15 includes five (5) interchangeable blades
- Non-skid stand for stability, folds for compact storage
- Easy-clean stainless steel body
- Each set includes an easy-grip stainless steel hand guard

	ITEM	DESCRIPTION	UOM	CASE
	MDL-18	Mandoline Slicer Set, 3 Built-in Blade Styles	Set	1/8
	MDL-15	Mandoline Slicer Set, 5 Interchangable Blades	Set	1/8
	MDL-BLD	5-Blade Set for MDL-15	Set	12/48
	MDL-HD	Hand Guard for MDL-15	Each	12/36

MANDOLINE SLICER SET

- Built-in julienne, and reversible slicing & serrated blades at varying thicknesses
- Non-skid, folding stand for compact storage
- Rotary adjustment dial
- Plastic body with rubberized; easy-grip hand guard

ITEM	DESCRIPTION	UOM	CASE	_
MDL-4P	Mandoline Slicer Set	Set	1/8	-

JAPANESE MANDOLINE SLICER SET

- Sharp blades for clean cuts
- Built-in blade adjusts thickness
- Great for carrots, onions, cucumbers and more
- Hand guard included

		0		
02-	ITEM	DESCRIPTION	UOM	CASE
	MDL-5P	Japanese Mandoline Slicer Set	Set	1/36
	MDL-5PBS	3-Blade Set for MDL-5P	Set	1



MDL-15

Slicina



MDL-18

MDL-15 with MDL-HD

MDL-4P